


Lens Dimensions (units in mm)



Specifications

Camera Information

Focal Length	12.5 mm
Aperture	F1.4
Lens D-FOV	46.6°
Lens H-FOV	39°
Lens V-FOV	30.3°
TTL	54.03 mm
MBFL	11.73 mm
MOD	0.15 m
TV Distortion	-0.8%
Image Size	2/3"
Resolution	5MP
Focusing Range (m)	0.15~∞
Shooting Range at MO.D.	110 mm x 82.5 mm
Filter Thread	M30.5×P0.5 mm

Environmental and Mechanical

Operating Temperature	20°C to +60°C
Size	Ø32.9×42.3 mm
Weight	60 grams
Material	Metal
Operation Focal	Manual with Lock
Operation Zoom	Fixed
Operation Iris	Manual with Lock
Mount Type	C-Mount

Order Information

Part Number	Description
C2305500FF	C-Mount Lens 12mm Fixed Focal Length Aperture Range From F1.4 ~ Close Up To 5 Megapixel Resolution



Compatible With C-Mount Cameras