


### Lens Dimensions (units in mm)



### Specifications

#### Camera Information

Focal Length	50 mm
Aperture	F1.4
Lens D-FOV	13.04°
Lens H-FOV	10.46°
Lens V-FOV	7.86°
TTL	74.43 mm
MBFL	11.93 mm
MOD	0.3 m
TV Distortion	-0.8%
Image Size	2/3"
Resolution	5MP
Focusing Range (m)	0.3~∞
Shooting Range at MO.D.	53.01 mm x 39.76 mm
Filter Thread	M37xP0.5 mm

#### Environmental and Mechanical

Operating Temperature	20°C to +60°C
Size	$\varnothing 39.6 \times 62.5$ mm
Weight	128 grams
Material	Metal
Operation Focal	Manual with Lock
Operation Zoom	Fixed
Operation Iris	Manual with Lock
Mount Type	C-Mount

### Order Information

Part Number	Description
C2305500FF	C-Mount Lens 50mm Fixed Focal Length Aperture Range From F1.4 ~ F16 Up To 5 Megapixel Resolution



Compatible With C-Mount Cameras